



vestige

CLEAR FLD

Transparent and fluid lab addition silicone used for composite injection moulding.

Description / Use

Transparent and fluid vinylpolysiloxane. It is suitable for counter mould in composite moulding techniques with a transparent muffle. Especially suitable for extensive works.

Standard packaging REF 1L5000

VESTIGE CLEAR FLD: 2x50ml cartridges + 6 mixing tips

Standard packaging REF 1L5001

VESTIGE CLEAR FLD: 4x50ml cartridges

Characteristics

- Fluid
- Transparent
- Rigid after setting
- Dimensional stability
- Practical
- Easy to mix

Advantages

- Flowing, it reproduces impressions without the development of bubbles
- It doesn't interfere with the resin polymerization and reduces its inhibited layer
- It doesn't deform
- Accurate and unaltered in time impressions
- Specific for extensive and complex works
- Packaged in standard 50ml cartridges

TECHNICAL DATA	VESTIGE CLEAR FLD
Mixing ratio	1:1
Mixing time (23°C)	Automix
Total working time (23°C)	1'
Setting time (23°C)	12'
Hardness	74 Shore "A"
Linear dimensional change	< 0,20%
Elastic recovery	>99,5%